
Shinko SE Series

SPEC SHEET

1ch Alarm Detector (DC Voltage) (with two large displays)

Model: SEIVA



Input Specifications

DC voltage


| Input range | Input resistance | Allowable signal |
|-------------|------------------|-------------------|
| | | source resistance |
| 0 to 1V DC | - 1MΩ | 2kΩ or less |
| 0 to 5V DC | | 1kΩ or less |
| 1 to 5V DC | | |
| 0 to 10V DC | | |


Output Specifications

A maximum of 6 points of alarm output available. For each alarm output, one of the following types can be selected in [Alarm type]: High limit alarm, Low limit alarm, High limit alarm with standby and Low limit alarm with standby.


High limit alarm

Low limit alarm





High limit alarm with standby
Low limit alarm with standby




Standby functions.

Alarm action: ON/OFF action Alarm hysteresis: 0.1 to 100.0%FS Alarm delay time: 0 to 9999 sec Alarm Energized/De-energized, Selectable Alarm HOLD function Enabled/Disabled, Selectable Alarm 1, 2 outputs: Relay contact 1a Control capacity: 3A 250V AC (resistive load) 1A 250V AC (inductive load $\cos\phi=0.4$) Electric life: 100,000 cycles Alarm 3 to 6 outputs: Open collector Control capacity: 0.1A 24V DC Performance Reference accuracy (Ambient temperature: 23°C) • DC voltage input: Within ±0.1% Indication accuracy: Within Reference input accuracy ±1 digit Input sampling period: 25msec, 125msec, 250msec (Selectable by keypad)

Temperature coefficient: $\pm 0.015\%/^{\circ}$ or less Insulation resistance: $10M\Omega$ or more, at 500V DC (Input - Output - Power) Dielectric strength: 1.5kV AC for 1 minute (Input - Output - Power)

General Structure

Case: Flame-resistant resin Color: Light gray Front panel: Membrane sheet Setting: Using the front keypad Display: Input display: 7-segment Red LED display 4-digit, Character size, 10x4.6mm (HxW) Set value display: 7-segment Red LED display 4-digit, Character size, 10x4.6mm (HxW) Power indicator: Green LED





Installation Specifications

Power supply: 100 to 240V AC 50/60Hz 24V AC/DC 50/60Hz Allowable voltage range: 85 to 264V AC, 20 to 28V AC/DC Power consumption: Approx. 9VA Ambient temperature: -5 to 55°C Ambient humidity: 35 to 85%RH (non-condensing) Mounting: DIN rail External dimensions: W30xH88xD108mm (socket included) Weight: Approx. 200g (socket included)

Attached Functions

Auto-light function: Automatically measures and controls brightness of the displays to conserve power. Power failure countermeasure:

The data is backed up in non-volatile IC memory. Self diagnosis: The CPU is monitored by a watchdog timer, and when an abnormal status is found on the CPU, the unit is switched to warm-up status turning all outputs OFF.

Environmental Specification

RoHS directive compliance

Settings

Function keys

- (1) UP Key: Increases a numerical value.
- (2) DOWN Key: Decreases a numerical value.
- (3) MODE Key: Selects a setting mode.
- (4) SUB-MODE Key: Re-lights displays. (UP Key, DOWN Key or MODE Key also re-lights displays.)

Displays and Indicator

- Input display: Indicates the input value. Indication of -2000 or less: The minus (-) sign and input value light alternately. Indication of 10000 or more: The lower 4 digits flash.
- Under range: -10% of input span or less: "----" flashes on the Input display.

Over range: 110% of input span or more:


- " " flashes on the Input display. Warm-up indication: The input type is indicated on the Input display for 3 seconds after power is turned ON.
- Set value display: Alarm 1 (A1) to Alarm 6 (A6) values are indicated (follows the selection in "Display selection".). If the UP Key is pressed for 1 second during alarm value indication, alarm values will be switched thus. $(A1 \rightarrow A2 \cdots A6 \rightarrow A1)$.


When power is turned ON, A1 value is indicated. When alarm output is ON, " $\vec{H} \perp \vec{n}$ " and the value selected in [Display selection] are alternately indicated on the Set value display. If the UP Key is pressed together with the DOWN Key in the above status, the alarm output currently being turned ON will be displayed. (E.g.) If Alarm 1 and Alarm 3 outputs are ON, "


and " $\Box \beta \vec{\beta}$ " are displayed in order.

Power indicator: The green LED is lit when power is turned ON.


Ferrules








Alarm 1, 2 outputs: Take the following measures for relay contact protection and noise reduction.



DC power



Alarm 3 to 6 outputs: Connection example of Open collector output

